

APC Back-UPS 600

Affordable Battery Backup For Home and Office Computers.

Extreme voltage fluctuations, surges and unexpected power cuts can damage today's desktop computers and even worse, cause loss of your valuable data. APC's Back-UPS RS 600 offers protection from these damaging power disturbances. Specifically designed for the rugged power conditions in India, this Back-UPS features Automatic Voltage Regulation, enabling you to work through poor power conditions while preserving battery capacity. Staged charging also recharges your battery faster so you're ready for the next power cut.



Product Features & Benefits:

- 1 "Boost" Automatic Voltage Regulation** corrects undervoltages without draining the battery, saving battery life for power cuts.
- 2 Visual and audible alarms** provide status of unit.
- 3 "Battery Backup & Surge Protected" outlets** keep a computer, monitor and other device running during power cuts, as well as protecting against damaging surges.
- 4 "Staged Charging"** recharges your battery faster so it's ready for the next power cut.
- 5 Push Button Circuit Breaker** enables quick recovery from overload.
- 6 2 Year Limited Warranty:** covers parts & labor, including battery
- 7 Automatic Diagnostic Testing** ensures your unit is ready when you need it.
- 8 1.2 meter power cord** with 6A Indian plug.

Back-UPS 600 Specifications

Model Number	BR600CI-IN
Output	
Output Capacity	600 VA / 360 Watts
Output Voltage / Frequency (On utility)	230V / 50Hz
Output Voltage / Frequency (On battery)	230V +/-8%, 50 Hz +/-1Hz
Output Connections	Three (3) India 3-pin 6 Amp sockets (all with battery backup and surge protection)
Waveform Type	Stepped Approximation to Sine Wave
Input	
Input Voltage / Frequency	230V / 50 Hz
Input Connection	India 6 Amp plug, 1.2 meter power cord
Physical	
Unit Dimensions (H x W x D)	185 x 115 x 213 mm
Unit Weight	5.7 Kg
Shipping Dimensions (H x W x D)	257 x 190 x 291 mm
Shipping Weight	6.1 Kg
Color	Black
UPC Code	731304282181
Battery	
Battery Type	7.5AH Maintenance-free, sealed lead-acid
Management	
Alarms	Visual (LED) and audible alarms
Adjustable Sensitivity and Transfer Voltage	Low, Medium, High

Typical Runtimes

Monitor size & type:

	15" LCD	17" LCD	19" LCD	22" LCD	17" CRT
Entry Level PC	26 min	21 min	17 min	12 min	11 min
Performance PC	14.5 min	12.5 min	10.5 min	8.5 min	7.5 min

For more information on runtimes, go to: www.apc.com/sizing

APC India
27, Lavelle Road,
Bangalore 560 001

APC Corporate
132 Fairgrounds Rd.
West Kingston, RI, 02892 USA

Customer Service:
Toll free (BSNL Network): 1-800-4254-272
All other networks: (add city code) 39022272

indiainfo@apc.com

www.apc.com/in

