

Product datasheet

Specifications



RACK PDU, BASIC, HALF HEIGHT, 100-240V/20A, 220-240V/16A, (14) C13

AP6003A

Overview

Lead time Usually in Stock

Main

Main Input Voltage 230 V

Main Output Voltage 100 V
120 V
200 V
208 V
230 V
240 V

Input Connection Type IEC 60320 C20

Number of rack unit 0U

Provided equipment Installation guide
Safety guide

Physical

Colour Black

Height 52.3 cm

Width 5.6 cm

Depth 4.7 cm

Net weight 1.88 kg

Mounting location Side

Mounting preference Lower

Mounting mode Not rack-mountable

USB compatible No

Input

[In] rated current 16 A

Permissible voltage 100...240 V

Max line current 20 A

Input current limits 20 A

Load capacity 3300 VA

Network frequency 50/60 Hz

Output

Number of power socket outlets 14 IEC 60320 C13

Conformance

Product certifications cUL listed
UL listed

Environmental

Ambient air temperature for operation 0...50 °C

Relative humidity 5...95 %

Operating altitude 0...10000 ft

Ambient air temperature for storage -15...65 °C

Storage Relative Humidity 5...95 %

Storage altitude 0.00...15240.00 m

Packing Units

Package 1 Weight 2.55 kg

Package 1 Height 61.2 cm

Package 1 width 12.3 cm

Package 1 Length 10.7 cm

SCC14 10731304327766

Number of Units in Package 3 96

Offer Sustainability

Sustainable offer status Green Premium product

REACH Regulation [REACH Declaration](#)

EU RoHS Directive Compliant
[EU RoHS Declaration](#)

Lead free Yes

Optimized Energy Efficiency Energy efficient product

Take-back Take-back program available

Contractual warranty

Warranty 2 years repair or replace