# **Product datasheet**

Specifications





# RACK PDU, BASIC, 0U/1U, 120-240V/15A, 220-240V/10A, (8) C13

AP6015A

#### Overview

Lead Time

Usually in Stock

#### Main

Colour	Black
Pdu Type	Basic
Provided Equipment	Installation guide Safety guide

## Complementary

Complementary		
Input Voltage	100 V	
	120 V	
	200 V	
	208 V	
	230 V	
	240 V	
Height	24 cm	
Width	4.4 cm	
Output Voltage	100 V	
	120 V	
	200 V	
	208 V	
	230 V	
	240 V	
Depth	9.3 cm	
Net Weight	0.91 kg	
Mounting Location	Front	
	Rear	
Mounting Preference	No preference	
Input Plug Type	IEC 60320 C14	
Mounting Mode	Not rack-mountable	
Rack Units	1U	
Mounting Position	Horizontal	
[In] Rated Current	12 A	
Permissible Voltage	100240 V	
Max Line Current	15 A	
Input Current Limits	15 A	
Load Capacity	2300 VA	



Network Frequency	50/60 Hz
Total Number Of Outlets	8 IEC 60320 C13

## Environment

Product Certifications	cUL listed CE EAC IRAM
	UL listed VDE

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	28.6 cm
Package 1 Width	13 cm
Package 1 Length	21 cm
Package 1 Weight	1.37 kg
Scc14	10731304327797

## **Contractual warranty**

Warranty

2 years repair or replace



# Sustainability

Green Premium<sup>TM</sup> label is Schneider Electric's commitment to delivering products with best-inclass environmental performances. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.



Energy Efficient Take-back Transparency RoHS/REACh

#### **Resource performance**

Energy Efficient Product

Take-Back Program Available

#### Well-being performance

Lead Free

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information



