

Product datasheet

Specifications



Rack PDU, Metered, Zero U, 10A, 230V, (16) C13

AP7850B

Overview

Lead time Usually in Stock

Main

Main Input Voltage	200 V 208 V 230 V
Main Output Voltage	230 V
Input Connection Type	IEC 60320 C14
Number of rack unit	0U
Cable length	3.05 m
Number of cables	1
Provided equipment	Cord retention bracket(s) Installation guide Rack mounting brackets Toolless mounting kit

Physical

Colour	Black
Height	124.5 cm
Width	5.6 cm
Depth	4.4 cm
Net weight	3.07 kg
Mounting location	Side
Mounting preference	No preference
Mounting mode	Rack-mounted

Input

Permissible voltage	200...250 V
Max line current	10 A
Load capacity	2300 VA
Network frequency	47...63 Hz

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Output

Number of power socket outlets	16 IEC 60320 C13
--------------------------------	------------------

Conformance

Product certifications	CE GOST VDE
------------------------	-------------------

Environmental

Ambient air temperature for operation	-5...45 °C
---------------------------------------	------------

Relative humidity	5...95 %
-------------------	----------

Operating altitude	0...10000 ft
--------------------	--------------

Ambient air temperature for storage	-25...65 °C
-------------------------------------	-------------

Storage Relative Humidity	5...95 %
---------------------------	----------

Storage altitude	0.00...15240.00 m
------------------	-------------------

Packing Units

Package 1 Weight	3.98 kg
------------------	---------

Package 1 Height	213.4 cm
------------------	----------

Package 1 width	38.7 cm
-----------------	---------

Package 1 Length	32.3 cm
------------------	---------

Offer Sustainability

Sustainable offer status	Green Premium product
--------------------------	-----------------------

REACH Regulation	REACH Declaration
------------------	-----------------------------------

EU RoHS Directive	Compliant EU RoHS Declaration
-------------------	--

Lead free	Yes
-----------	-----

Mercury free	Yes
--------------	-----

RoHS exemption information	Yes
----------------------------	---------------------

Optimized Energy Efficiency	Energy efficient product
-----------------------------	--------------------------

Take-back	Take-back program available
-----------	-----------------------------

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------