Specifications





# APC NetShelter Switched Rack PDU, 1U, 1PH, 3.7kW 230V 16A or 3.3kW 208V 16A, 8 C13 outlets, C20 cord

AP7921B

Presentation	This APC Switched Rack PDU power distribution unit has a wide range of standardized PDU features that increase network efficiency, manageability and functionality. The output and input connections are (8)C13. Network management capabilities allow you to configure and manage rack PDUs from remote locations. It has has a local current monitoring display that gives a visible warning in case of an overload. The remote individual outlet control provides real-time monitoring of connected loads. It has a multi-tier user access that enables you to restrict unauthorized use of outlets. This rack has a single input power source making it easy to install.
Lead Time	Usually in Stock

wain	
Colour	Black
Pdu Type	Switched
Cord Length	2.50 m
Number Of Cables	1
Provided Equipment	Installation guide Rack mounting brackets User manual

## Complementary

Input Voltage	200 V
	208 V
	230 V
Height	4.4 cm
Width	44.5 cm
Output Voltage	208 V
	230 V
Depth	10.8 cm
Net Weight	2.27 kg
Mounting Location	Front
	Rear
Mounting Preference	No preference
Input Plug Type	IEC 60320 C20
Mounting Mode	Rack-mounted
Rack Units	1U
Mounting Position	Horizontal
[In] Rated Current	16 A



Permissible Voltage	200240 V
Input Current Limits	20 A
Load Capacity	3680 VA
Network Frequency	50/60 Hz
Outlet Type And Quantity	8 IEC 60320 C13

## Environment

Product Certifications	cUL listed CE CSA GOST IRAM MIC UL listed VDE VCCI
Standards	EN 55022 class A EN 55024 EN 61000-3-2 EN 61000-3-3 UL 60950
Ambient Air Temperature For Operation	045 °C
Relative Humidity	095 %
Operating Altitude	010000 ft
Ambient Air Temperature For Storage	-2565 °C
Storage Relative Humidity	095 %
Storage Altitude	0.0015240.00 m

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7 cm
Package 1 Width	34.3 cm
Package 1 Length	47 cm
Package 1 Weight	3.45 kg

## **Contractual warranty**

Warranty

2 years repair or replace

# Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performances. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.



Energy Efficient Take-back Transparency RoHS/REACh

#### **Resource performance**

Zenergy Efficient Product

Take-Back Program Available

#### Well-being performance

Mercury Free

Rohs Exemption Information Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information



