

Product datasheet

Specifications



Power Cord Kit (6 ea), Locking, C13 to C14, 1.8m, Red

AP8706S-WWX340

Overview

Lead time Usually in Stock

Main

Input Connection Type IEC 60320 C14

Cable length 1.83 m

Physical

Colour Red

Height 24 cm

Width 7.5 cm

Depth 5.5 cm

Net weight 1.35 kg

Mounting preference No preference

Mounting mode Not rack-mountable

Input

Max line current 10 A

Input current limits 10 A

Output

Max current draw 10 A

Number of power socket outlets 1 IEC 60320 C13

Power cable length 1.83 m

Conformance

Product certifications CCC
PSE
VDE

Environmental

Ambient air temperature for operation 0...70 °C

Relative humidity	20...80 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-25...75 °C
Storage Relative Humidity	20...80 %
Storage altitude	0.00...15240.00 m

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	24 cm
Package 1 Width	5.5 cm
Package 1 Length	7.5 cm
Package 1 Weight	1.35 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Recommended replacement(s)