



# Power Cord Kit (6 ea), Locking, C19 to C20, 1.2m, Blue

AP8714SX592

#### **Overview**

Lead Time Usually in Stock

#### Main

Input Connection Type	IEC 60320 C20
Cable Length	1.22 m
Number Of Cables	6

### **Physical**

Colour	Blue
Height	30 cm
Width	7 cm
Depth	7 cm
Net Weight	1.64 kg
Mounting Preference	No preference
Mounting Mode	Not rack-mountable

## Input

Max Line Current	16 A
Input Current Limits	16 A

## **Output**

Max Current Draw	16 A
Number Of Power Socket Outlets	1 IEC 60320 C19
Power Cable Length	1.22 m

#### **Conformance**

Product Certifications	CCC	
	CSA	
	PSE	
	UL listed	
	VDE	

#### **Environmental**

Ambient Air Temperature For Operation	075 °C
Relative Humidity	2080 %

Operating Altitude	010000 ft
Ambient Air Temperature For Storage	-2575 °C
Storage Relative Humidity	2080 %
Storage Altitude	0.00 15240.00 m

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	30 cm
Package 1 Width	7 cm
Package 1 Length	7 cm
Package 1 Weight	1.64 kg
Scc14	10731304285004

# **Contractual warranty**

Warranty 2 years repair or replace



Green Premium<sup>TM</sup> label is Schneider Electric's commitment to delivering products with best-inclass environmental performances. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

Learn more about Green Premium >







Take-back Transparency RoHS/REACh

#### Resource performance



Take-Back Program Available

#### Well-being performance



Lead Free

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information