

APC Dry Contact I/O Accessory



AP9810

Overview

Presentation	UPS management accessory that provides two dry contact input and one relay output interface to APC UPS management offers with UIO ports such as the UPS Network Management Card (AP9641, AP9643) or Dry Contact I/O SmartSlot Card (AP9613).
Lead Time	Usually in Stock

Main

Provided Equipment	Cat 5 Ethernet cable
	User manual

Physical

Colour	Black
Height	2.2 cm
Width	4.52 cm
Depth	4.46 cm
Net Weight	0.05 kg
Mounting Preference	No preference
Mounting Mode	Not rack-mountable

Conformance

Standards	EN 61000-4-2	
	EN 61000-4-3	
	EN 61000-4-4	
	EN 61000-4-6	

Environmental

Ambient Air Temperature For Operation	040 °C
Operating Altitude	03333 ft
Relative Humidity	095 %
Ambient Air Temperature For Storage	-1565 °C
Storage Altitude	0.004572.00 m
Storage Relative Humidity	095 %

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Package 1 Height	3.300 cm
Package 1 Width	25.400 cm
Package 1 Length	12.700 cm
Package 1 Weight	140.000 g
Unit Type Of Package 2	PAM
Number Of Units In Package 2	576
Package 2 Height	123.000 cm
Package 2 Width	120.000 cm
Package 2 Length	100.000 cm
Package 2 Weight	80.960 kg

Contractual warranty

Warranty 2 years repair or replace



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performances. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Learn more about Green Premium >









Energy Efficient Take-back Transparency RoHS/REACh

Resource performance

Energy Efficient Product

✓ Take-Back Program Available

Well-being performance

L

Lead Free

Certifications & Standards

Reach Regulation

Eu Rohs Directive

Compliant

EU RoHS Declaration

Environmental Disclosure

Product Environmental Profile

The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins