

Product datasheet

Specifications



APC Rack PDU 9000 Switched, ZeroU, 16A, 100-240V, (21) C13/C15 & (3) C19/C21, Japan

APDU9959J

Overview

Lead time Usually in Stock

Main

Main Input Voltage	200 V
Main Output Voltage	200 V
Input Connection Type	IEC 60320 L6-20P
Number of rack unit	0U
Communication port protocol	SNMP Redfish
Provided equipment	Installation guide Rack mounting brackets Safety guide

Physical

Colour	Black
Height	179.7 cm
Width	5.5 cm
Depth	4.6 cm
Net weight	5.55 kg
Mounting location	Side
Mounting preference	No preference
Mounting mode	Not rack-mountable
USB compatible	No

Input

[In] rated current	16 A
Permissible voltage	100...240 V
Input current limits	20 A
Load capacity	3300 VA
Network frequency	50/60 Hz

Output

Number of power socket outlets	21 C13/C15 3 C19/C21
--------------------------------	-------------------------

Conformance

Product certifications	FCC part 15 class A PSE
------------------------	----------------------------

Environmental

Ambient air temperature for operation	-5...60 °C
---------------------------------------	------------

Relative humidity	5...95 %
-------------------	----------

Operating altitude	0...10000 ft
--------------------	--------------

Ambient air temperature for storage	-25...65 °C
-------------------------------------	-------------

Storage Relative Humidity	5...95 %
---------------------------	----------

Storage altitude	0.00...15240.00 m
------------------	-------------------

Batteries & Runtime

Communication network type	10/100/1000BASE-T
----------------------------	-------------------

Packing Units

Package 1 Weight	7.86 kg
------------------	---------

Package 1 Height	200.2 cm
------------------	----------

Package 1 width	16.5 cm
-----------------	---------

Package 1 Length	11.4 cm
------------------	---------

Number of Units in Package 3	48
------------------------------	----

Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------

WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
------	---

Contractual warranty

Warranty	3 years repair or replace
----------	---------------------------