

Product datasheet

Specifications



APC ADVANCED SURGEARREST 5 OUTLET FRENCH 230V

E20-FR

⚠ Discontinued on: 10 June 2022

E20-FR has not been replaced. Please contact your customer care centre for more information.

⚠ Discontinued

Overview

Lead time Usually in Stock

Main

Main Input Voltage 230 V

Number of cables 1

Provided equipment User manual

Physical

Colour Beige

Height 5.84 cm

Width 31.12 cm

Depth 12.7 cm

Net weight 0.91 kg

Mounting preference No preference

Mounting mode Not rack-mountable

Input

Maximum line current 10 A

Network frequency 50/60 Hz +/- 5 Hz auto-sensing

Output

Number of power socket outlets 5

Outlet standard French/Belgian

Conformance

Product certifications CE

Environmental

Ambient air temperature for operation 0...40 °C

Relative humidity	0...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-15...45 °C
Storage Relative Humidity	0...95 %
Storage altitude	0.00...15240.00 m

Surge Protection and Filtering

Response time	0 ns common mode
Common mode rejection	70 dB
Peak current	11 kA common mode 13 kA normal mode
Surge energy rate	480 J

Packing Units

Package 1 Weight	1.09 kg
Package 1 Height	6.35 cm
Package 1 width	31.75 cm
Package 1 Length	18.41 cm
SCC14	10731304009679
Number of Units in Package 2	12
Package 2 Weight	14.24 kg
Number of Units in Package 3	384

Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------