


Product datasheet

Specifications



Galaxy VX 250kVA 400/480V Power Cabinet

GVXP250KD

Overview

Lead Time	Special Order - Call for Quoted Lead Times
-----------	--

Main

Main Input Voltage	480 V 3 phases
Main Output Voltage	480 V 3 phases
Rated Power In W	250000 W
Rated Power In Va	250000 VA

Physical

Colour	White
Height	197 cm
Width	60 cm
Depth	90 cm
Net Weight	540 kg

Output

Maximum Configurable Power In W	250000 W
---------------------------------	----------

Environmental

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 % non-condensing
Ambient Air Temperature For Storage	-15...40 °C
Storage Relative Humidity	0...95 % non-condensing

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	215 cm
Package 1 Width	106 cm
Package 1 Length	74 cm
Package 1 Weight	696 kg


Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performances. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

[Learn more about Green Premium >](#)

Well-being performance

	Rohs Exemption Information	Yes
<hr/>		
Reach Regulation	REACH Declaration	
<hr/>		
Eu Rohs Directive	Compliant with Exemptions	
<hr/>		
China Rohs Regulation	China RoHS declaration	
<hr/>		