

Product datasheet

Specifications



APC Smart-UPS SRT 8000VA 208V

SRT8KXLT

Overview

Presentation	High density, double-conversion on-line power protection with scalable runtime.
Lead time	Usually in Stock

Main

Main Input Voltage	208 V
Other Input Voltage	240 V
Main Output Voltage	208 V
Other Output Voltage	240 V
Rated power in W	8000 W
Rated power in VA	8000 VA
Nb of power socket outlets	4 NEMA L6-20R 2 NEMA L6-30R 1
Output connector type	Hard wire 3-wire (2P + E) 1
Battery type	Lead-acid battery
Provided equipment	CD with software Documentation CD Installation guide Temperature probe USB cable Warranty card Web/SNMP management card

General

Product web sub-family	High density
Number of power module free slots	0
Number of power module filled slots	0
Redundant	No

Physical

Colour	Black
Height	43.2 cm
Width	26.3 cm

Depth	71.5 cm
Net weight	111.58 kg
Mounting location	Front
Mounting preference	No preference
Mounting mode	Rack-mounted with kit
Two post mountable	0
USB compatible	Yes

Input

Network frequency	40...70 Hz auto-sensing
Number of input connectors	1 hard wire 3-wire (2P + E)
Input voltage limits	100...275 V adjustable (half load)

Output

Maximum configurable power in W	8000 W
Harmonic distortion	Less than 2 %
Output frequency	50/60 Hz +/- 3 Hz sync to mains
Crest factor	3 : 1
UPS type	Double conversion online
Wave type	Sine wave
Bypass type	Internal bypass (automatic and manual)
Maximum configurable power in VA	8000 VA

Conformance

Product certifications	ENERGY STAR V2.0 (USA) FCC part 15 class A NOM UL 1778
------------------------	---

Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 % non-condensing
Operating altitude	0...10000 ft
Ambient air temperature for storage	-15...45 °C
Storage Relative Humidity	Non-condensing 0...95 %
Storage altitude	0.00...15240.00 m
Acoustic level	55 dBA
Heat dissipation	1712 Btu/h
IP degree of protection	IP20

Batteries & Runtime

Number of battery filled slots	0
Battery recharge time	1.5 h

Number of battery replacement quantity	2
Battery voltage	+/- 192 V (split battery referenced to neutral)
Battery charger power	1136 W rated
Battery power in VAH	1716 VAh runtime
Battery life	3...5 year(s)
Battery option	SRT192BP2 1 3432 VAh SRT192BP2 2 5148 VAh SRT192BP2 3 6864 VAh SRT192BP2 4 8580 VAh SRT192BP2 5 10296 VAh SRT192BP2 6 12012 VAh SRT192BP2 8 15444 VAh SRT192BP2 10 18876 VAh
Extended runtime	1

Communications & Management

Free slots	1
Control panel	Multifunction LCD status and control console
Alarm	Audible and visible alarms prioritized by severity
Emergency power off	Yes


Surge Protection and Filtering

Surge energy rate	480 J
-------------------	-------

Packing Units

Package 1 Weight	126.55 kg
Package 1 Height	46.1 cm
Package 1 width	60 cm
Package 1 Length	100 cm
Number of Units in Package 3	1

Offer Sustainability

Sustainable offer status	Green Premium product
Energy Star	ENERGY STAR UPS V2.0 (USA) 
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	3 years repair or replace (excluding battery) and 2 years for battery
----------	---