

# Product datasheet

Specifications



## Rack ATS, 120V, 30A, L5-30P in, (16) 5-20R out



AP4453

! Discontinued on: 08 March 2023

! To be end-of-service on: 08 March 2025

! Discontinued - Service only

### Overview

Lead time Usually in Stock

### Main

Main Input Voltage	120 V
Main Output Voltage	120 V
Input Connection Type	NEMA L5-30P
Number of rack unit	2U
Cable length	2.44 m
Number of cables	2
Provided equipment	Mounting hardware Rack mounting brackets Serial configuration cable

### Physical

Colour	Black
Height	8.8 cm
Width	43.2 cm
Depth	23.6 cm
Net weight	6.33 kg
Mounting location	Front Rear
Mounting preference	No preference
Mounting mode	Rack-mounted

### Input

Network frequency	50/60 Hz
[In] rated current	24 A
Max line current	30 A
Input current limits	30 A
Load capacity	2880 VA

## Output

Max current draw	30 A
Number of power socket outlets	16 NEMA 5-20R
Protection type	Circuit breaker

## Conformance

Standards	EN 55022 class A FCC part 15 class A
-----------	---

## Environmental

Ambient air temperature for operation	-5...45 °C
Relative humidity	5...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-25...65 °C
Storage Relative Humidity	5...95 %
Storage altitude	0.00...15240.00 m

## Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	21 cm
Package 1 Width	35.6 cm
Package 1 Length	58.4 cm
Package 1 Weight	8.82 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Lead free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>
Take-back	Take-back program available

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

## Recommended replacement(s)

AP4453 is replaced by:

---

1x



APC NetShelter Rack Automatic Transfer Switch, 2U, 30A, 120V, 2 L5-30P IN, 16  
5-20R OUT, 50/60Hz

AP4453A

---