

Product datasheet

Specifications



APC 19" Rack LCD Console

AP5719

Overview

Presentation	1U rack-mountable keyboard, mouse, and LCD console with US English keyboard layout.
Lead time	Usually in Stock

Main

Main Input Voltage	100 V 240 V
Number of rack unit	1U
Provided equipment	C13-C14 power cord Documentation CD Firmware upgrade cable Installation guide NEMA 5-15 power cord PS2 KVM cable Rack mounting hardware Single user rack mount kit USB cable USB KVM cable

Physical

Colour	Black
Height	4.4 cm
Width	48.2 cm
Depth	66.5 cm
Net weight	17.4 kg
Mounting location	Front Rear
Mounting preference	No preference
Mounting mode	Rack-mounted
Maximum mounting depth	104.98 cm
Minimum mounting depth	68 cm

Input

Network frequency	50/60 Hz
--------------------------	----------

Conformance

Product certifications	C-Tick CE
-------------------------------	--------------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Industry Canada
KCC
NOM
UL listed
VCCI class A
VDE
TAA compliance

Standards	EN 55022 class A EN 55024 EN 60950 FCC part 15 class A IEC 60950
------------------	--

Environmental

Ambient air temperature for operation	0...40 °C
--	-----------

Supported Hardware

Display size	19 inch
Trackball type	PS/2 touchpad USB mouse
Display type	LCD display
Display power consumption	19 W
Pixel size	0.26

Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	15.2 cm
Package 1 Width	82.6 cm
Package 1 Length	67.3 cm
Package 1 Weight	20.99 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Lead free	Yes
Mercury free	Yes
RoHS exemption information	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
-----------------	---------------------------

Recommended replacement(s)