

Product datasheet

Specifications



Rack PDU, Basic, 0U/1U, 208V, 30A, (4) C19



AP6031A

Overview

Lead time Usually in Stock

Main

Main Input Voltage	200 V 208 V
PDU type	Basic
Main Output Voltage	200 V 208 V
Input Connection Type	NEMA L6-30P
Number of rack unit	1U
Cable length	3.66 m
Provided equipment	Installation guide Safety guide

Physical

Colour	Black
Height	4.4 cm
Width	43.8 cm
Depth	12.6 cm
Net weight	3.8 kg
Mounting location	Front Rear
Mounting preference	No preference
Mounting mode	Not rack-mountable
USB compatible	No

Input

[In] rated current	24 A
Max line current	30 A
Input current limits	30 A
Load capacity	5000 VA
Network frequency	50/60 Hz

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Output

Number of power socket outlets 4 IEC 60320 C19

Conformance

Product certifications cUL listed
UL listed

Packing Units

Unit Type of Package 1 Db

Number of Units in Package 1 1

Package 1 Height 28.1 cm

Package 1 Width 18 cm

Package 1 Length 47.3 cm

Package 1 Weight 4.6 kg

SCC14 10731304327810

Offer Sustainability

Sustainable offer status Green Premium product

REACH Regulation [REACH Declaration](#)

EU RoHS Directive Compliant
[EU RoHS Declaration](#)

Lead free Yes

Optimized Energy Efficiency Energy efficient product

Take-back Take-back program available

Contractual warranty

Warranty 2 years repair or replace

Recommended replacement(s)