

Product datasheet

Specifications

Power Cord Kit (6 ea), Locking, C19 to C20, 0.6m



AP8712S

Overview

Presentation Free up space and secure power cords between rack-mount PDUs and attached IT equipment with this exclusive easy-to-use cord retention method. While these cords will fit into any standard IEC receptacle or power inlet; the "locking" feature is enabled only when used with APC AP8000 series Rack PDUs or IT equipment with built-in locking receptacles. These locking connectors reduce the probability of accidentally disconnecting cords and dropping loads.

Lead time Usually in Stock

Main

Input Connection Type IEC 60320 C20

Cable length 0.61 m

Number of cables 6

Physical

Colour Black

Height 30 cm

Width 6 cm

Depth 6.5 cm

Net weight 1.12 kg

Mounting preference No preference

Mounting mode Not rack-mountable

Input

Max line current 16 A

Input current limits 16 A

Output

Max current draw 16 A

Number of power socket outlets 1 IEC 60320 C19

Power cable length 0.61 m

Conformance

Product certifications CCC
CSA
PSE

UL listed
VDE

Environmental

Ambient air temperature for operation	0...75 °C
Relative humidity	20...80 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-25...75 °C
Storage Relative Humidity	20...80 %
Storage altitude	0.00...15240.00 m

Packing Units

Package 1 Height	30 cm
Package 1 Width	6 cm
Package 1 Length	6.5 cm
Package 1 Weight	1.12 kg
Unit Type of Package 2	CAR
Number of Units in Package 2	1
Package 2 Height	29.99 cm
Package 2 Width	5.99 cm
Package 2 Length	6.5 cm
Package 2 Weight	1.15 kg
Unit Type of Package 3	PAL
Number of Units in Package 3	1
Package 3 Height	143.99 cm
Package 3 Width	100 cm
Package 3 Length	120 cm
Package 3 Weight	1.16 kg
SCC14	10731304279683

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Lead free	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Recommended replacement(s)