

# Product data sheet

Specifications



Power Cord Kit (6 ea), Locking, C13 to C14, 1.2m (4ft), North America, Blue

AP8704S-NAX590

## Overview

Lead Time	Usually in Stock
-----------	------------------

## Main

Input Connection Type	IEC 60320 C14
Cable Length	4 ft (1.22 m)
Number Of Cables	6

## Physical

Colour	Blue
Height	9.45 in (24 cm)
Width	2.76 in (7 cm)
Depth	1.77 in (4.5 cm)
Net Weight	2.23 lb(US) (1.01 kg)
Mounting Preference	No preference
Mounting Mode	Not rack-mountable

## Input

Max Line Current	10 A
Input Current Limits	10 A

## Output

Max Current Draw	10 A
Number Of Power Socket Outlets	1 IEC 60320 C13
Power Cable Length	4 ft (1.22 m)

## Conformance

Product Certifications	CSA UL listed
------------------------	------------------

## Environmental

Ambient Air Temperature For Operation	32...221 °F (0...105 °C)
Relative Humidity	20...80 %
Operating Altitude	0...10000 ft

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient Air Temperature For Storage	-13...221 °F (-25...105 °C)
Storage Relative Humidity	20...80 %
Storage Altitude	0...50000 ft (0.00...15240.00 m)

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.45 in (24 cm)
Package 1 Width	1.77 in (4.5 cm)
Package 1 Length	2.76 in (7 cm)
Package 1 Weight	2.23 lb(US) (1.01 kg)

## Contractual warranty


Warranty	2 years repair or replace
----------	---------------------------


Sustainability




**Green Premium™** label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

[Learn more about Green Premium >](#)







Take-back

Transparency


RoHS/REACH

Resource performance



Take-Back Program Available

Well-being performance



Lead Free

Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>