
# Product data sheet







AP9563

### **Overview**

| Lead Time Usually in Stock |  |
|----------------------------|--|
|----------------------------|--|

#### Main

| Colour             | PL I                                      |
|--------------------|---|
| Colour             | Black                                     |
| Pdu Type           | Basic                                     |
| Cord Length        | 12 ft (3.66 m)                            |
| Number Of Cables   | 1   |
| Provided Equipment | Installation guide Rack mounting brackets |

### Complementary

| Input Voltage           | 100 V<br>120 V       |
|-------------------------|----------------------|
| Height                  | 1.73 in (4.4 cm)     |
| Width                   | 17.60 in (44.7 cm)   |
| Output Voltage          | 120 V                |
| Depth                   | 2.24 in (5.7 cm)     |
| Net Weight              | 5.51 lb(US) (2.5 kg) |
| Mounting Location       | Front<br>Rear        |
| Mounting Preference     | No preference        |
| Input Plug Type         | NEMA 5-20P           |
| Mounting Mode           | Rack-mounted         |
| Rack Units              | 1U                   |
| Mounting Position       | Horizontal           |
| [In] Rated Current      | 16 A                 |
| Input Current Limits    | 20 A                 |
| Load Capacity           | 1920 VA              |
| Network Frequency       | 50/60 Hz             |
| Total Number Of Outlets | 10 NEMA 5-20R        |

### **Environment**

| Product Certifications | cUL listed |
|------------------------|------------|
|                        | UL listed  |

| Ambient Air Temperature For Operation | 23113 °F (-545 °C)         |
|---------------------------------------|----------------------------|
| Relative Humidity                     | 095 %                      |
| Operating Altitude                    | 010000 ft                  |
| Ambient Air Temperature For Storage   | -13149 °F (-2565 °C)       |
| Storage Relative Humidity             | 095 %                      |
| Storage Altitude                      | 050000 ft (0.0015240.00 m) |

# **Packing Units**

| Unit Type Of Package 1       | PCE                   |
|------------------------------|-----------------------|
| Number Of Units In Package 1 | 1                     |
| Package 1 Height             | 2.76 in (7 cm)        |
| Package 1 Width              | 9.02 in (22.9 cm)     |
| Package 1 Length             | 18.27 in (46.4 cm)    |
| Package 1 Weight             | 8.02 lb(US) (3.64 kg) |

## **Contractual warranty**

Warranty 2 years repair or replace



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

Learn more about Green Premium >









Energy Efficient Take-back Transparency RoHS/REACh

### Resource performance

Energy Efficient Product

✓ Take-Back Program Available

### Well-being performance

Lead Free

### **Certifications & Standards**

Reach Regulation

Eu Rohs Directive

Compliant

EU RoHS Declaration

Environmental Disclosure

Product Environmental Profile

Circularity Profile

End of Life Information