

Product data sheet

Specifications



APC NetShelter Rack PDU Advanced, Switched, 3PH, 22.1kW 400V 32A or 17.3kW 415V 30A, 48 Outlets, IEC309

APDU10350SW

Overview

Lead time Usually in Stock

Main

Main Input Voltage	415 V 3 phases 400 V 3 phases
Product or component type	PDU
PDU type	Switched
Main Output Voltage	240 V
Input Connection Type	IEC 60309 30 A 3P + N + PE
Number of rack unit	0U
Cable length	5.91 ft (1.8 m)
Communication port protocol	1000BASE-T 10/100BASE-T

Physical

Colour	Black
Height	70.08 in (178.0 cm)
Width	2.20 in (5.6 cm)
Depth	2.95 in (7.5 cm)
Net weight	21.16 lb(US) (9.6 kg)
Mounting location	Side
Mounting preference	No preference
Mounting mode	Rack-mounted

Input

[In] rated current	24 A
Permissible voltage	200...240 V 346...415 V
Input current limits	30 A
Load capacity	17300 VA
Network frequency	50/60 Hz

Output

Number of power socket outlets	24 C13/C15/C19/C21 24 C13/C15
--------------------------------	----------------------------------

Conformance

Product certifications	UKCA TAA compliance
Standards	UL 62368-1 CSA C22.2 No 62368-1 FCC part 15 Subpart B CE EN 62368-1
IP degree of protection	IP44

Environmental

Ambient air temperature for operation	23...140 °F (-5...60 °C)
Relative humidity	5...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	5...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	77.95 in (198 cm)
Package 1 Width	5.20 in (13.2 cm)
Package 1 Length	10.31 in (26.2 cm)
Package 1 Weight	27.78 lb(US) (12.6 kg)

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
RoHS exemption information	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	3 years repair or replace
----------	---------------------------

Recommended replacement(s)