Product data sheet

Specifications





APC NetShelter 13U Wallmount Rack Cabinet Vented Door Double Hinged Server Depth

AR100HD

Overview

Presentation

Ideal for retail, healthcare, and educational facilities, the wall rack offers an efficient solution for deploying server and networking equipment for edge computing applications. For areas with limited floor space. Designed to house your server, as well as network solutions such as network switches and patch panels. Rack hinges at the rear allowing for access to the back of the rack during installation and setup or while undergoing maintenance. The door is reversible allowing for the door to open direction desired to avoid interference with its surroundings. Optional 120V fan tray top-mounted and caster kit. Several APC Smart-UPS models low-profile provide easy UPS integration and mounting. 13U Wall mount cabinet, 19 inches maximum mounting depth, 200lb weight capacity, 19" rack width, ships fully assembled, vented door, 5 year APC warranty.

Lead Time

Usually in Stock

Main

Product Or Component Type	Rack enclosure
Number Of Rack Unit	13U
Number Of Cables	1
Provided Equipment	Key(s) User manual Wall-mounting template

Physical

Height	26.10 in (66.3 cm)
Width	22.99 in (58.4 cm)
Depth	24.84 in (63.1 cm)
Net Weight	94.20 lb(US) (42.73 kg)
Colour	Black
Mounting Preference	No preference
Mounting Mode	Not rack-mountable
Maximum Mounting Depth	19.00 in (48.26 cm)
Rack Width	19"
Marking	16 gauge EIA mounting rail 16 gauge front door 16 gauge post 13 gauge rear door 18 gauge roof 18 gauge side panels
Permanent Permissible Load	200 lb(US) (90.72 kg) static

Conformance



Standards EIA-310E

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	32.99 in (83.8 cm)
Package 1 Width	27.01 in (68.6 cm)
Package 1 Length	30.51 in (77.5 cm)
Package 1 Weight	115.02 lb(US) (52.17 kg)

Contractual warranty

Warranty 5 year repair or replace



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Learn more about Green Premium >







Take-back Transparency RoHS/REACh

Resource performance



Take-Back Program Available

Well-being performance



Reach Free Of Svhc



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile