# Product data sheet

Specification





# APC NetShelter 12U Wallmount Rack Cabinet Single Hinged Server Depth Unassembled

AR112

#### Overview

Presentation

Ideal for retail, healthcare, and educational facilities, the wall rack offers an efficient solution for deploying server and networking equipment for edge computing applications. For areas with limited floor space. Designed to house your server, as well as network solutions such as network switches and patch panels. Rack hinges at the rear allowing for access to the back of the rack during installation and setup or while undergoing maintenance. The door is reversible allowing for the door to open direction desired to avoid interference with its surroundings. Optional 120V fan tray top-mounted and caster kit. Several APC Smart-UPS models low-profile provide easy UPS integration and mounting. 12U Wall mount cabinet, 16.8 to 20.8 inches mounting depth, 200lb weight capacity, 19" rack width, ships unassembled, 5 year

APC warranty

Usually in Stock

Main

Lead Time

Product Or Component Type Rack enclosure

Number Of Rack Unit 12U

### **Physical**

Height	24.41 in (62 cm)
Width	23.58 in (59.9 cm)
Depth	23.58 in (59.9 cm)
Net Weight	40.30 lb(US) (18.28 kg)
Colour	Black
Mounting Support	Wall
Mounting Preference	No preference
Mounting Mode	Not rack-mountable
Maximum Mounting Depth	20.80 in (52.83 cm)
Minimum Mounting Depth	16.80 in (42.67 cm)
Rack Width	19"
Permanent Permissible Load	200 lb(US) (90.72 kg) static

#### **Conformance**

Standards EIA-310E

#### **Packing Units**

Unit Type Of Package 1	PCE
Number Of Unite In Deckers 4	

Disclaimer. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	11.54 in (29.3 cm)
Package 1 Width	26.89 in (68.3 cm)
Package 1 Length	27.09 in (68.8 cm)
Package 1 Weight	50.99 lb(US) (23.13 kg)

# **Contractual warranty**

Warranty 5 year repair or replace



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

Learn more about Green Premium >







Take-back Transparency RoHS/REACh

## Resource performance



Take-Back Program Available

## Well-being performance



Reach Free Of Svhc



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile