



# Network UPS 12Vdc. Lithium Battery,19500mAh, BMS, 4LED

CP12142LI

### **Overview**

Lead Time Usually in Stock

#### Main

Main Input Voltage	12 V DC
Product Or Component Type	Uninterruptible power supply (UPS)
Main Output Voltage	12 V DC
Rated Power In W	38 W
Rated Power In Va	140 VA
Battery Type	Li-lon (Lithium-lon)
Provided Equipment	User manual

## **Batteries & Runtime**

Number Of Battery Filled Slots	0
Number Of Battery Free Slots	0
Battery Recharge Time	24 h

## **Physical**

Width	7.40 in (18.8 cm)
Depth	3.78 in (9.6 cm)
Net Weight	1.65 lb(US) (0.75 kg)
Mounting Preference	No preference
Mounting Mode	Not rack-mountable
Two Post Mountable	0
Usb Compatible	No
Height	3.78 in (9.6 cm)

## **Output**

Maximum Configurable Power In W

## **Conformance**

Standards	FN 55000 along A
Standards	EN 55022 class A
	EN 55024
	EN 61000-3-2
	EN 61000-3-3
	FCC part 15 class B
Equipment Protection Policy	Lifetime : \$25000

## **Environmental**

Ambient Air Temperature For Operation	32113 °F (045 °C)
Relative Humidity	095 % non-condensing
Operating Altitude	010000 ft
Ambient Air Temperature For Storage	23113 °F (-545 °C)
Storage Relative Humidity	095 % non-condensing
Storage Altitude	050000 ft (0.0015240.00 m)

# **Communications & Management**

Control Panel	LED status display with on line : on battery : replace battery and overload indicators
Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.69 in (17 cm)
Package 1 Width	6.10 in (15.5 cm)
Package 1 Length	3.86 in (9.8 cm)
Package 1 Weight	2.25 lb(US) (1.02 kg)
Scc14	10731304338748

## **Contractual warranty**

Warranty 2 years repair or replace



**Green Premium**<sup>TM</sup> label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Learn more about Green Premium >









Energy Efficient Take-back Transparency RoHS/REACh

## Resource performance



**Energy Efficient Product** 



Take-Back Program Available

## Well-being performance



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information