

Product data sheet

Specifications



FRP, 120VAC, 60HZ, 60V, 9 AMPS

CTFRP6009

⚠ Discontinued on: Dec 31, 2022

⚠ End-of-service on: Dec 31, 2022

⚠ Discontinued - Service only

Overview

Lead Time Usually Ships within 2 Weeks

Main

Rated Power In W	540 W
Rated Power In Va	540 VA
Output Connection Type	1 NEMA 5-15R surge
Number Of Rack Unit	0U
Provided Equipment	User manual

Physical

Height	11.50 in (29.21 cm)
Width	6.00 in (15.24 cm)
Depth	6.00 in (15.24 cm)
Net Weight	29.56 lb(US) (13.41 kg)
Mounting Location	Front
Mounting Mode	Not rack-mountable
Usb Compatible	No

Input

Network Frequency	60 Hz +/- 3 Hz
-------------------	----------------

Output

Maximum Configurable Power In W	540 W
---------------------------------	-------

Environmental

Ambient Air Temperature For Operation	-40...140 °F (-40...60 °C)
---------------------------------------	----------------------------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	15.00 in (38.1 cm)
Package 1 Width	10.00 in (25.4 cm)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Length	10.00 in (25.4 cm)
Package 1 Weight	40.00 lb(US) (18.142 kg)
Number Of Units In Package 2	0
Package 2 Weight	0 lb(US) (0.00 kg)

Contractual warranty

Warranty	1 year (parts only)
----------	---------------------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

[Learn more about Green Premium >](#)

Eu Rohs Directive

Under investigation
