

Product data sheet

Specifications



Galaxy VS 9Ah Smart Long-Life High Capacity Battery Module

GVSBTHULL

Overview

Presentation	One long-life 9 Ah battery module for the Galaxy VS UPS.
Lead time	Usually Ships within 2 Weeks

Main

Battery type	VRLA
---------------------	------

Physical

Height	6.30 in (16 cm)
Width	5.12 in (13 cm)
Depth	30.71 in (78 cm)
Net weight	70.55 lb(US) (32 kg)

Environmental

Ambient air temperature for operation	64...81 °F (18...27 °C)
Relative humidity	0...95 % non-condensing
Ambient air temperature for storage	32...104 °F (0...40 °C)
Storage Relative Humidity	10...80 % non-condensing

Batteries & Runtime

Device mounting	Enclosed battery cabinet
Battery power in VAh	1080 VAh

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.09 in (18 cm)
Package 1 Width	31.50 in (80 cm)
Package 1 Length	5.91 in (15 cm)
Package 1 Weight	72.75 lb(US) (33 kg)

Offer Sustainability

EU RoHS Directive

Not applicable, out of EU RoHS legal scope

Recommended replacement(s)