

Product data sheet

Specifications

NetBotz Leak Rope Sensor - 20 ft.

NBES0308



Overview

Presentation	Provides early detection of fluid in your data center or network closet along the entire length. Compatible with select NetBotz appliances.
Lead time	Usually Ships within 2 Weeks

General

Provided equipment	Cable ties
---------------------------	------------

Physical

Depth	6.34 in (16.1 cm)
Height	2.76 in (7 cm)
Net weight	0.97 lb(US) (0.44 kg)
Width	6.73 in (17.1 cm)

Environmental

Ambient air temperature for operation	32...113 °F (0...45 °C)
Operating altitude	0...10000 ft
Relative humidity	0...95 %
Ambient air temperature for storage	5...149 °F (-15...65 °C)
Storage altitude	0...50000 ft (0.00...15240.00 m)
Storage Relative Humidity	0...95 %

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.80 in (7.1 cm)
Package 1 Width	9.21 in (23.4 cm)
Package 1 Length	6.42 in (16.3 cm)
Package 1 Weight	1.14 lb(US) (0.519 kg)

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS declaration
RoHS exemption information	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Recommended replacement(s)