

产品参数表

规格



机柜ATS，230V，10A，C14输入， (12) C13输出



AP4421

待中断日期 30 十二月 2022

待中断

概要

外观

The APC Rack Automatic Transfer Switch (ATS) is a high availability switch that provides redundant power to connected equipment and has two input power cords, one for each AC source. The output configuration is (12) IEC 60320 C13. The Rack ATS supplies power to the connected load from a primary AC source. If that primary source becomes unavailable, the Rack ATS automatically transfers loads to the secondary source. The transfer time from one source to the other is seamless to the connected equipment, as the switching occurs safely between the two input sources regardless of any phase differences. The units have built-in network connectivity, which allows for remote management through Web, SNMP, SSH, Telnet, or StruxureWare™ Data Center Expert. With multiple outlets, several devices can be plugged directly into the Rack ATS without the need for an additional Rack PDU. Current monitoring and alarms help prevent downtime to the equipment by providing aggregate current measurements and warnings when power consumption draws near the maximum rating of the Rack ATS. Built-in network and local interfaces allow for custom configuration settings for added flexibility.

交期

通常现货供应

主要信息

Main Input Voltage	230 V
Main Output Voltage	230 V
Input Connection Type	IEC 60320 C14
机架单元数	2U
设备提供	安装配件 架式安装支架 串行配置电缆

物理参数

颜色	黑色
高度	4.4 cm
宽度	43.2 cm
深度	23.6 cm
产品净重	3.93 kg
安装位置	正面 后面
Mounting preference	No preference
安装类型	Rack-mounted

输入

网络频率	50/60 Hz
------	----------

Max line current	10 A
Input current limits	10 A
负载容量	2000 VA

输出

最大总负载电流	10 A
Number of power socket outlets	12 IEC 60320 C13
保护类型	Without circuit breaker

相符性

符合标准	EN 55022 A 级 FCC 15 部分 A 级
------	-------------------------------

环境

运行温度	-5...45 °C
相对湿度	5...95 %
工作海拔	0...10000 ft
贮存环境温度	-25...65 °C
存储相对湿度	5...95 %
存储高度	0.00...15240.00 m

包装单位

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.4 cm
Package 1 Width	34.9 cm
Package 1 Length	60 cm
Package 1 Weight	5.7 kg

可持续性

产品类型	Green Premium 产品
REACH法规	REACH 声明
欧盟ROHS指令	符合 欧盟ROHS声明
无铅	是
无汞	是
RoHS 豁免信息	是
环境披露	产品环境文件
流通资料	产品使用寿命终期信息
Take-back	Take-back program available

合同保修

保修单	2年内维修或更换
-----	----------

推荐的替代产品