



# Power Cord Kit (6 ea), Locking, C13 to C14, 1.2m, Blue

AP8704S-WWX590

#### Overview

Lead Time Usually in Stock

#### Main

Cable Length 1.22 m **Number Of Cables** 

## **Physical**

•		
Colour	Blue	
Height	24 cm	
Width	7 cm	
Depth	4.5 cm	
Net Weight	1.01 kg	
Mounting Preference	No preference	
Mounting Mode	Not rack-mountable	

## Input

Max Line Current	10 A
Input Current Limits	10 A

## **Output**

Max Current Draw	10 A	
Number Of Power Socket Outlets	1 IEC 60320 C13	
Power Cable Length	1.22 m	

### **Conformance**

<b>Product Certifications</b>	CCC
	PSE
	VDE

### **Environmental**

Ambient Air Temperature For Operation	070 °C
Relative Humidity	2080 %
Operating Altitude	010000 ft
Ambient Air Temperature For Storage	-2575 °C

Storage Relative Humidity	2080 %
Storage Altitude	0.0015240.00 m

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	24 cm
Package 1 Width	4.5 cm
Package 1 Length	7 cm
Package 1 Weight	1.01 kg

# **Contractual warranty**

Warranty 2 years repair or replace

Apr 23, 2024



**Green Premium**<sup>TM</sup> label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Learn more about Green Premium >







Take-back Transparency RoHS/REACh

### Resource performance



Take-Back Program Available

### Well-being performance



Lead Free

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information