Product datasheet

Specifications





LI Replacement Battery Cartridge #181 LI

RBCV181-LI

Overview

Lead Time

Lleuglly	in	Stock
Usually	In	STOCK

Main

Product Or Component Type	Replacement battery cartridge
Battery Type	Li-Ion (Lithium-Ion)
Provided Equipment	Installation guide

Batteries & Runtime

Battery Location	Internal battery
Number Of Battery Free Slots	0
Number Of Battery Filled Slots	0
Battery Voltage	38.4 V
Number Of Battery Replacement Quantity	1

Physical

Height	7.6 cm
Width	20 cm
Depth	25 cm
Net Weight	4.3 kg
Mounting Mode	Not rack-mountable

Output

Battery Capacity

6 Ah

Conformance

Product Certifications

cULus UN 38.3

Environmental

Ambient Air Temperature For Operation	050 °C
Operating Altitude	03000 m
Relative Humidity	095 %
Ambient Air Temperature For Storage	-2060 °C



Storage Altitude	015000 m
Storage Relative Humidity	095 %

Packing Units

PCE
1
19.5 cm
37 cm
32 cm
5.4 kg

Contractual warranty

Warranty

5 years repair or replace



Sustainability

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.



Mercury Free Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

