

# Product datasheet

Specifications



## RACK PDU, BASIC, VERTICAL, 220-240V, 32A, (20) C13, (6) C19

AP6009A

### Overview

Lead time Usually in Stock

### Main

Main Input Voltage	230 V
Main Output Voltage	230 V
Input Connection Type	IEC 60309 32 A 2P + E
Number of rack unit	0U
Cable length	3.05 m
Number of cables	1
Provided equipment	Installation guide Safety guide

### Physical

Height	162.6 cm
Width	5.6 cm
Depth	4.3 cm
Net weight	6.18 kg
Mounting location	Side
Mounting preference	No preference
Mounting mode	Not rack-mountable

### Input

Permissible voltage	200...240 V
Input current limits	32 A
Load capacity	7400 VA
Network frequency	50/60 Hz

### Output

Number of power socket outlets	20 IEC 60320 C13 6 IEC 60320 C19
--------------------------------	-------------------------------------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Conformance

Product certifications	CE EAC IRAM VDE
------------------------	--------------------------

## Environmental

Ambient air temperature for operation	0...50 °C
Relative humidity	5...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-15...65 °C
Storage Relative Humidity	5...95 %
Storage altitude	0.00...15240.00 m

## Packing Units

Package 1 Weight	8 kg
Package 1 Height	187.5 cm
Package 1 width	22.6 cm
Package 1 Length	13.5 cm
Number of Units in Package 3	35

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Lead free	Yes
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------