

Product datasheet

Specifications



APC NetShelter Switched Rack PDU, 1U, 1PH, 2.3kW 230V 10A or 2.5kW 208V 12A, 8 C13 outlets, C14 cord

AP7920B

Overview

Presentation This APC Switched Rack PDU power distribution unit has a wide range of standardized PDU features that increase network efficiency, manageability and functionality. The output and input connections are (8)C13. Network management capabilities allow you to configure and manage rack PDUs from remote locations. It has a local current monitoring display that gives a visible warning in case of an overload. The remote individual outlet control provides real-time monitoring of connected loads. It has a multi-tier user access that enables you to restrict unauthorized use of outlets. This rack has a single input power source making it easy to install.

Lead Time Usually in Stock

Main

Colour	Black
Pdu Type	Switched
Cord Length	1.98 m
Number Of Cables	1
Provided Equipment	Installation guide Rack mounting brackets User manual

Complementary

Input Voltage	200 V 208 V 230 V
Height	4.4 cm
Width	44.5 cm
Output Voltage	208 V 230 V
Depth	10.8 cm
Net Weight	2.27 kg
Mounting Location	Front Rear
Mounting Preference	No preference
Input Plug Type	IEC 60320 C14
Mounting Mode	Rack-mounted
Rack Units	1U
Mounting Position	Horizontal
[In] Rated Current	12 A

Permissible Voltage	200...240 V
Input Current Limits	15 A
Load Capacity	2300 VA
Rated Current	10 A - 230 V 12 A - 208 V
Network Frequency	50/60 Hz
Outlet Type And Quantity	8 IEC 60320 C13

Environment

Product Certifications	cUL listed CE CSA GOST IRAM UL listed VDE
Standards	EN 55022 class A EN 55024 EN 61000-3-2 EN 61000-3-3 UL 60950
Ambient Air Temperature For Operation	0...45 °C
Relative Humidity	0...95 %
Operating Altitude	0...10000 ft
Ambient Air Temperature For Storage	-25...65 °C
Storage Relative Humidity	0...95 %
Storage Altitude	0.00...15240.00 m

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7 cm
Package 1 Width	34.3 cm
Package 1 Length	47 cm
Package 1 Weight	3.45 kg

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

[Learn more about Green Premium >](#)



Energy Efficient Take-back Transparency RoHS/REACH

Resource performance

Energy Efficient Product

Take-Back Program Available

Well-being performance

Mercury Free

Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive [Compliant with Exemptions](#)

Environmental Disclosure [Product Environmental Profile](#)

Circularity Profile [End of Life Information](#)
