



Power Cord Kit (6 ea), Locking, C19 to C20, 0.6m (2ft), Blue

AP8712SX590

Overview

Lead Time Usually in Stock

Main

Input Connection Type	IEC 60320 C20
Cable Length	0.61 m
Number Of Cables	6

Physical

Colour	Blue
Height	30 cm
Width	6 cm
Depth	6.5 cm
Net Weight	1.12 kg
Mounting Preference	No preference
Mounting Mode	Not rack-mountable

Input

Max Line Current	16 A
Input Current Limits	16 A

Output

Max Current Draw	16 A
Number Of Power Socket Outlets	1 IEC 60320 C19
Power Cable Length	0.61 m

Conformance

Product Certifications	CCC	
Troduct our timeations		
	CSA	
	PSE	
	UL listed	
	VDE	

Environmental

Ambient Air Temperature For Operation	075 °C
Relative Humidity	2080 %

Operating Altitude	010000 ft
Ambient Air Temperature For Storage	-2575 °C
Storage Relative Humidity	2080 %
Storage Altitude	0.00 15240.00 m

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	30 cm
Package 1 Width	6.5 cm
Package 1 Length	6 cm
Package 1 Weight	1.12 kg

Contractual warranty

Warranty 2 years repair or replace



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Learn more about Green Premium >







Take-back Transparency RoHS/REACh

Resource performance



Take-Back Program Available

Well-being performance



Lead Free

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information