

# Power Cord, C19 to C14, 2.0m

AP9878



#### **Overview**

Lead Time Usually in Stock

#### Main

Input Connection Type	IEC 60320 C14
Cable Length	1.98 m
Number Of Cables	1

## **Physical**

Colour	Black
Net Weight	0.28 kg
Mounting Preference	No preference
Mounting Mode	Not rack-mountable

## Input

Max Line Current 10 A

## Output

Max Current Draw	10 A
Number Of Power Socket Outlets	1 IEC 60320 C19

#### **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	30.5 cm
Package 1 Width	10.2 cm
Package 1 Length	10.2 cm
Package 1 Weight	0.359 kg
Unit Type Of Package 2	CAR
Number Of Units In Package 2	10
Package 2 Height	23.5 cm
Package 2 Width	33.5 cm
Package 2 Length	53 cm
Package 2 Weight	4.3 kg

Unit Type Of Package 3	PAL
Number Of Units In Package 3	10
Package 3 Height	143.99 cm
Package 3 Width	100 cm
Package 3 Length	120 cm
Package 3 Weight	4.3 kg

## **Contractual warranty**

Warranty 2 years repair or replace



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

Learn more about Green Premium >







Take-back Transparency RoHS/REACh

### Resource performance



Take-Back Program Available

#### Well-being performance



Lead Free

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information