

Product datasheet

Specifications



APC Replacement battery cartridge #140 with 2 Year Warranty

APCRBC140

Overview

Lead time Usually in Stock

Main

Battery type Lead-acid battery

Provided equipment Battery recycling guide

Physical

Colour Black

Height 12.2 cm

Width 19.7 cm

Depth 59.7 cm

Net weight 34.55 kg

Mounting mode Not rack-mountable

Environmental

Ambient air temperature for operation 0...40 °C

Operating altitude 0...10000 ft

Relative humidity 0...95 % non-condensing

Ambient air temperature for storage -15...45 °C

Storage altitude 0.00...15240.00 m

Storage Relative Humidity 0...95 % Non-condensing

Batteries & Runtime

Number of battery free slots 0

Number of battery filled slots 0

Device mounting Enclosed battery cartridge

Battery voltage 192 V

Additional information Each APCRBC140 consists of 2 battery modules as shown in the product image.

Number of battery replacement quantity	1
--	---

Packing Units

Package 1 Weight	37.27 kg
------------------	----------

Package 1 Height	22.6 cm
------------------	---------

Package 1 width	40.9 cm
-----------------	---------

Package 1 Length	78.1 cm
------------------	---------

Number of Units in Package 3	20
------------------------------	----

Offer Sustainability

Sustainable offer status	Green Premium product
--------------------------	-----------------------

REACH Regulation	REACH Declaration
------------------	-----------------------------------

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
-------------------	---

Environmental Disclosure	Product Environmental Profile
--------------------------	---

Circularity Profile	End of Life Information
---------------------	---

Take-back	Take-back program available
-----------	-----------------------------

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------
