# **Product datasheet**

Specifications





## APC Replacement Battery Cartridge, VRLA battery, 5.1Ah, 192VDC, 2-year warranty

APCRBC140

#### Overview

Lead Time Usually in Stock

#### Main

Product Or Component Type	Replacement battery cartridge
Battery Type	Lead-acid battery
Provided Equipment	Battery recycling guide

#### **Batteries & Runtime**

Number Of Battery Free Slots	0
Number Of Battery Filled Slots	0
Device Mounting	Enclosed battery cartridge
Battery Voltage	192 V
Additional Information	Each APCRBC140 consists of 2 battery modules as shown in the product image.
Number Of Battery Replacement Quantity	1

### **Physical**

Colour	Black
Height	12.2 cm
Width	19.7 cm
Depth	59.7 cm
Net Weight	34.55 kg
Mounting Mode	Not rack-mountable

#### **Environmental**

Ambient Air Temperature For Operation	040 °C
Operating Altitude	010000 ft
Relative Humidity	095 % non-condensing
Ambient Air Temperature For Storage	-1545 °C
Storage Altitude	0.0015240.00 m
Storage Relative Humidity	095 % non-condensing

### **Packing Units**



Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	22.6 cm
Package 1 Width	78.1 cm
Package 1 Length	40.9 cm
Package 1 Weight	37.27 kg

## **Contractual warranty**

Warranty 2 years repair or replace



**Green Premium**<sup>TM</sup> label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Learn more about Green Premium >







Take-back Transparency RoHS/REACh

### Resource performance



Take-Back Program Available

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information