

Product datasheet

Specifications



APC Replacement battery cartridge #148 with 2 Year Warranty

APCRBC148

Overview

Lead time Usually in Stock

Main

Main Input Voltage	12 V DC
Product or component type	Replacement battery cartridge
Number of cables	1
Battery type	Lead-acid battery
Provided equipment	All required connectors Battery recycling guide Metallic battery tray or enclosure Reusable packaging Installation guide

Physical

Colour	Black
Height	8.3 cm
Width	21.6 cm
Depth	34.3 cm
Net weight	10 kg
Mounting mode	Not rack-mountable
USB compatible	No

Environmental

Ambient air temperature for operation	0...45 °C
Operating altitude	0...10000 ft
Relative humidity	0...95 %
Ambient air temperature for storage	-15...45 °C
Storage altitude	0.00...15240.00 m
Storage Relative Humidity	0...95 %

Batteries & Runtime

Number of battery free slots	0
Number of battery filled slots	0
Device mounting	Enclosed battery cartridge
Number of battery replacement quantity	1
Replacement battery	

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	15.2 cm
Package 1 Width	49.5 cm
Package 1 Length	36.8 cm
Package 1 Weight	10.91 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Lead free	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Recommended replacement(s)