

Product datasheet

Specifications



APC Replacement Battery Cartridge 175

APCRBC175

Overview

Lead Time Usually in Stock

Main

Main Input Voltage	12 V
Product Or Component Type	Replacement battery cartridge
Main Output Voltage	12 V
Battery Type	Lead-acid battery
Provided Equipment	User manual

Batteries & Runtime

Battery Location	Internal battery
Number Of Battery Blocks Per String	6
Number Of Battery Free Slots	0
Number Of Battery Filled Slots	0
Device Mounting	Built-in
Battery Voltage	12 V
Number Of Battery Replacement Quantity	1

Physical

Colour	Black
Height	151 mm
Width	99 mm
Depth	65 mm
Net Weight	2.68 kg
Mounting Preference	No preference
Mounting Mode	Not rack-mountable

Output

Battery Capacity 9 Ah

Conformance

Product Certifications UL 1778 5th edition

Standards	UL 1778 5th edition
-----------	---------------------

Environmental

Ambient Air Temperature For Operation	0...40 °C
---------------------------------------	-----------

Operating Altitude	0...10000 ft
--------------------	--------------

Relative Humidity	0...85 %
-------------------	----------

Ambient Air Temperature For Storage	-15...50 °C
-------------------------------------	-------------

Storage Altitude	0.00...3048.00 m
------------------	------------------

Storage Relative Humidity	0...95 %
---------------------------	----------

Packing Units

Unit Type Of Package 1	PCE
------------------------	-----

Number Of Units In Package 1	1
------------------------------	---

Package 1 Height	19.5 cm
------------------	---------

Package 1 Width	39.5 cm
-----------------	---------

Package 1 Length	49.5 cm
------------------	---------

Package 1 Weight	18 kg
------------------	-------

Sccl4	50731304427198
-------	----------------

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Sustainability


Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.


[Learn more about Green Premium >](#)



Transparency RoHS/REACH

Well-being performance

 Mercury Free

 RoHS Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Pro-active compliance (Product out of EU RoHS legal scope)
[EU RoHS Declaration](#)

China Rohs Regulation [China RoHS declaration](#)

Environmental Disclosure [Product Environmental Profile](#)

Circularity Profile [End of Life Information](#)