

# Product datasheet

Specifications



## APC NetShelter SX, Server Rack Enclosure, 48U, Black, 2258H x 600W x 1200D mm

AR3307

### Overview

<b>Presentation</b>	An industry-standard server rack ready for medium to high-density environments with height designed to easily fit through standard doorways. A deeper rack design provides enough rack mounting space for even the deepest devices and still plenty of room for vertically mounting Rack PDUs and cable management. 48U height allows for an additional 6U of rack mounting space maximizing u-space per rack footprint.
<b>Lead time</b>	Usually in Stock

### Main

<b>Number of rack unit</b>	48U
<b>Provided equipment</b>	Baying hardware Key(s) Leveling feet Mounting hardware Pre-installed casters Side panels

### Physical

<b>Colour</b>	Black
<b>Height</b>	225.8 cm
<b>Width</b>	60 cm
<b>Depth</b>	120 cm
<b>Net weight</b>	149.55 kg
<b>Mounting preference</b>	No preference
<b>Mounting mode</b>	Not rack-mountable
<b>Maximum mounting depth</b>	105.99 cm
<b>Minimum mounting depth</b>	19.1 cm
<b>Rack width</b>	19"
<b>Marking</b>	14 gauge EIA mounting rail 16 gauge front door 16 gauge post 18 gauge rear door 18 gauge roof 18 gauge side panels
<b>Permanent permissible load</b>	1020.58 kg dynamic 1700.97 kg static

### Conformance

<b>Standards</b>	UL 2416 UL 60950-1
------------------	-----------------------

## Packing Units

Package 1 Weight	165.45 kg
Package 1 Height	238.5 cm
Package 1 width	75.2 cm
Package 1 Length	133.4 cm
Number of Units in Package 3	1

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
Take-back	Take-back program available

## Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------