

# Product datasheet

Specifications



## Network Power supply with battery backup, 12Vdc, 1A, CEE7, lithium battery

CP12010LI-GR

### Overview

Lead Time Usually in Stock

### Main

Main Input Voltage	220 V 230 V 240 V
Main Output Voltage	12 V DC
Rated Power In W	12 W
Rated Power In Va	12 VA
Battery Type	Li-Ion (Lithium-Ion)

### Batteries & Runtime

Number Of Battery Filled Slots	0
Number Of Battery Free Slots	0

### Physical

Width	4.8 cm
Depth	7.6 cm
Net Weight	0.2 kg
Mounting Preference	No preference
Mounting Mode	Not rack-mountable
Two Post Mountable	0
Usb Compatible	No
Height	7.8 cm

### Output

Maximum Configurable Power In W	12 W
---------------------------------	------

### Conformance

Standards	EN 55024 EN 60950
-----------	----------------------

### Environmental

Ambient Air Temperature For Operation	0...40 °C
---------------------------------------	-----------

---

Relative Humidity	5...95 %
-------------------	----------

---

Ambient Air Temperature For Storage	-15...60 °C
-------------------------------------	-------------

---

## Packing Units

---

Unit Type Of Package 1	PCE
------------------------	-----

---

Number Of Units In Package 1	1
------------------------------	---

---

Package 1 Height	11.3 cm
------------------	---------

---

Package 1 Width	9.9 cm
-----------------	--------

---

Package 1 Length	5.2 cm
------------------	--------

---

Package 1 Weight	0.28 kg
------------------	---------

---

Scc14	10731304344091
-------	----------------

---

## Contractual warranty

---

Warranty	2 years repair or replace
----------	---------------------------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

[Learn more about Green Premium >](#)

## Well-being performance

✓ Toxic Heavy Metal Free

---

✓ Mercury Free

---

✓ Rohs Exemption Information [Yes](#)

---

**Reach Regulation** [REACH Declaration](#)

---

**Eu Rohs Directive** Compliant  
[EU RoHS Declaration](#)

---

**China Rohs Regulation** [China RoHS declaration](#)  
Pro-active China RoHS declaration (out of China RoHS legal scope)

---