

Product datasheet

Specifications



Network Power supply with battery backup, 12Vdc, 1A, CEE7, lithium battery

CP12010LI-GR

Overview

Lead Time	Usually in Stock
-----------	------------------

Main

Main Input Voltage	220 V 230 V 240 V
Product Or Component Type	Uninterruptible power supply (UPS)
Main Output Voltage	12 V DC
Rated Power In W	12 W
Rated Power In Va	12 VA
Battery Type	Li-Ion (Lithium-Ion)

Batteries & Runtime

Number Of Battery Filled Slots	0
Number Of Battery Free Slots	0

Physical

Width	4.8 cm
Depth	7.6 cm
Net Weight	0.2 kg
Mounting Preference	No preference
Mounting Mode	Not rack-mountable
Two Post Mountable	0
Usb Compatible	No
Height	7.8 cm

Output

Maximum Configurable Power In W	12 W
---------------------------------	------

Conformance

Standards	EN 55024 EN 60950
-----------	----------------------

Environmental

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	5...95 %
Ambient Air Temperature For Storage	-15...60 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.3 cm
Package 1 Width	9.9 cm
Package 1 Length	5.2 cm
Package 1 Weight	0.28 kg
Scc14	10731304344091

Contractual warranty




Warranty	2 years repair or replace
----------	---------------------------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

[Learn more about Green Premium >](#)

Well-being performance

	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Reach Regulation		REACH Declaration
Eu Rohs Directive		Compliant EU RoHS Declaration
China Rohs Regulation		China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)