

# Product datasheet

Specifications

## NetBotz Rack Monitor 750

NBRK0750



### Overview

Presentation	The NetBotz Rack Monitor 750 provides integrated surveillance, sensing, access control, and advanced alerting for IT environments of all sizes, from single-rack edge networks to large data centers.
Lead Time	Usually in Stock

### Main

Product Or Component Type	Industrial rack PC
Number Of Rack Unit	1U
Communication Port Protocol	A-Link DHCP HTTPS IPv4 SNMP v1 SNMP v3 SSH v2 TCP/IP
Provided Equipment	Rack mounting brackets Temperature/humidity sensor USB cable
Product Compatibility	Rack sensor pod 150 Room sensor pod 155

### General

Camera Frame Rate	Up to 30 fps
Display Resolution	Up to 1280x1024
Universal Sensor Supported	0-5V Door contact Dry contact Humidity Smoke Fluid spot leak Temperature Vibration
Number Of Universal Sensor Ports	6
Number Of Sensor Pods Supported	12
Number Of Universal Sensors Supported	78
Number Of Supported Camera	4

### Physical

Colour	Black
Height	4.3 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Width	43.2 cm
Depth	17.8 cm
Net Weight	2.45 kg
Mounting Location	Front Rear
Mounting Preference	No preference
Mounting Mode	Rack-mounted
Mounting Position	Horizontal

## Conformance

Standards	CSA C22.2 No. 60950-1-03 FCC part 15 class A ICES-003 UL 60950-1
Product Certifications	2014/30/EU AS/NZS 3548 (C-Tick) class A CE EMC directive 2004/108/EC VCCI class A

## Environmental

Ambient Air Temperature For Operation	0...40 °C
Operating Altitude	0...10000 ft
Relative Humidity	0...95 %
Ambient Air Temperature For Storage	-15...65 °C
Storage Altitude	0.00...15240.00 m
Storage Relative Humidity	0...95 %

## Communications & Management

Communication Network Type	RJ45 10/100/1000 Base-T
----------------------------	-------------------------

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	12.1 cm
Package 1 Width	31.8 cm
Package 1 Length	53.3 cm
Package 1 Weight	4.17 kg

## Contractual warranty



Warranty	2 years
----------	---------

## Sustainability

**Green Premium™** label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

[Learn more about Green Premium >](#)

## Well-being performance

 Mercury Free	
 Rohs Exemption Information	<a href="#">Yes</a>
Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins