

Product datasheet

Specifications



Accusine SWP Single 90A 400V IP20

PCS090Y4IP20U

ⓘ Discontinued

Overview

Lead Time Usually Ships within 3 Weeks

Main

Main Input Voltage	400 V 3 phases
Main Output Voltage	400 V 3 phases
Rated Power In W	0 W
Rated Power In Va	0 VA
Output Connector Type	Hard wire 4-wire (3P + E) 1 Hard wire 5-wire (3P + N + E) 1 Hard wire 4-wire (3P + PEN) 1
Provided Equipment	Installation guide User manual

Batteries & Runtime

Number Of Battery Filled Slots	0
Number Of Battery Free Slots	0

Physical

Height	78 cm
Width	59 cm
Depth	32.5 cm
Net Weight	230 kg
Mounting Preference	No preference
Mounting Mode	Rack-mounted
Two Post Mountable	0
Usb Compatible	No

Input

Network Frequency	50/60 Hz
Maximum Input Current	90 A

Output

Maximum Configurable Power In W	0 W
---------------------------------	-----

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environmental

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 %
Operating Altitude	0...3333 ft
Ambient Air Temperature For Storage	-25...65 °C
Storage Relative Humidity	0...95 %
Storage Altitude	0.00...9144.00 m
Acoustic Level	65 dBA
Ip Degree Of Protection	IP20

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	67 cm
Package 1 Width	80 cm
Package 1 Length	84 cm
Package 1 Weight	263 kg

Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

[Learn more about Green Premium >](#)

Well-being performance

✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
Eu Rohs Directive		Compliant EU RoHS Declaration
China Rohs Regulation		China RoHS declaration Product out of China RoHS scope. Substance declaration for your information