



APC IT Power Distribution Module 3x1 Pole 3 Wire 32A 3xIEC309 660cm, 720cm, 780cm

PDM1332IEC-3P-3

Overview

Presentation	Factory assembled and tested Power Distribution Modules include circuit breaker, power cord, power connection, and circuit monitoring. Auto-detection of modules by the Modular PDU minimizes installation time.
Lead Time	Usually Ships within 3 Weeks

Main

Main Input Voltage	400 V 3 phases
Main Output Voltage	230 V
Provided Equipment	Installation guide

Physical

_		
Colour	Grey	
Height	15.2 cm	
Width	43.2 cm	
Depth	43.2 cm	
Net Weight	6.39 kg	

Input

Network Frequency	50 Hz
Max Line Current	32 A

Output

Max Current Draw	32 A
Number Of Power Socket Outlets	3 IEC 309 32 A 2P + E

Conformance

Product Certifications	CE
	VDE

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	15.2 cm
Package 1 Width	43.2 cm

Package 1 Length	43.2 cm
Package 1 Weight	7.3 kg

Contractual warranty

Warranty 1 year repair or replace



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Learn more about Green Premium >







Take-back Transparency RoHS/REACh

Resource performance



Take-Back Program Available

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information