Product datasheet





Power Dist. Mod. 3 Pole 5 Wire RCD 16A 30mA IEC309 140CM

PDM316IEC-30R-140

! Discontinued on: Dec 20, 2023



Overview

Presentation	Factory assembled and tested Power Distribution Modules include circuit breaker, power cord, power connection, and circuit monitoring. Auto-detection of modules by the Modular PDU minimizes installation time.
Lead Time	Usually Shins within 4 Weeks

Main

Main Input Voltage	400 V 3 phases
Main Output Voltage	230 V 400 V 3 phases
Provided Equipment	Installation guide

Physical

Colour	Grey	
Height	25.4 cm	
Width	43.2 cm	
Depth	40.6 cm	
Net Weight	1.7 kg	

Input

Network Frequency	50 Hz
Max Line Current	16 A

Output

Max Current Draw	16 A
Number Of Power Socket Outlets	1 IEC 309 16 A

Conformance

Product Certifications	CE
	VDE

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	25.4 cm

Life Is On APC

Package 1 Width	40.6 cm
Package 1 Length	43.2 cm
Package 1 Weight	2.6 kg

Contractual warranty

Warranty 1 year repair or replace



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Learn more about Green Premium >







Take-back Transparency RoHS/REACh

Resource performance



Take-Back Program Available

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information