# **Product datasheet**

Specifications





APC Replacement Battery Cartridge, Valve regulated lead– acid battery, 7Ah, 12VDC, 2-year warranty

RBC2

#### Overview

Lead Time Usually in Stock

#### Main

Replacement battery cartridge
1
Lead-acid battery
All required connectors Battery recycling guide Reusable packaging Installation quide

#### **Batteries & Runtime**

Number Of Battery Free Slots	0
Number Of Battery Filled Slots	0
Battery Voltage	12 V
Number Of Battery Replacement Quantity	1

## **Physical**

Colour	Black
Height	9.4 cm
Width	6.4 cm
Depth	15.1 cm
Net Weight	2.5 kg
Mounting Mode	Not rack-mountable
Usb Compatible	No

#### **Output**

Battery Capacity 7.0 Ah

#### **Environmental**

Ambient Air Temperature For Operation	040 °C
Operating Altitude	010000 ft
Relative Humidity	095 %
Ambient Air Temperature For Storage	-1545 °C

Life Is On APC

Storage Altitude	0.0015240.00 m
Storage Relative Humidity	0. 95 %

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.9 cm
Package 1 Width	17.5 cm
Package 1 Length	21.3 cm
Package 1 Weight	2.77 kg

## **Contractual warranty**

Warranty 2 years repair or replace



**Green Premium**<sup>TM</sup> label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Learn more about Green Premium >







Take-back Transparency RoHS/REACh

### Resource performance



Take-Back Program Available

### Well-being performance



Rohs Exemption Information

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information