

# Product datasheet

Specifications



## APC Replacement Battery Cartridge #32 with 2 Year Warranty

RBC32

### Overview

Lead time Usually in Stock

### Main

Product or component type Replacement battery cartridge

Battery type Lead-acid battery

Provided equipment All required connectors  
Battery recycling guide  
Reusable packaging  
Installation guide

### Physical

Colour Charcoal

Height 19.7 cm

Width 14.9 cm

Depth 6.4 cm

Net weight 5.33 kg

Mounting mode Not rack-mountable

### Output

Battery capacity 7.0 Ah

### Environmental

Ambient air temperature for operation 0...40 °C

Operating altitude 0...50000 ft

Relative humidity 0...95 %

Ambient air temperature for storage 0...40 °C

Storage altitude 0.00...3048.00 m

Storage Relative Humidity 0...95 %

### Batteries & Runtime

Battery location Internal battery

Number of battery blocks per string	2
Number of battery free slots	0
Number of battery filled slots	0
Device mounting	Enclosed battery cabinet
Battery voltage	24 V
Number of battery replacement quantity	1
Replacement battery	

## Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	30.5 cm
Package 1 Width	10.2 cm
Package 1 Length	22.9 cm
Package 1 Weight	5.91 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>
Take-back	Take-back program available

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

## Recommended replacement(s)