



APC Easy UPS 1 Ph Line Interactive, 2000VA, Tower, 230V, 6 Universal outlets, AVR, LCD

SMV2000AI-MS

#### Overview

Lead Time Usually in Stock

#### Main

wain	
Main Input Voltage	230 V
Input Voltage	220 V
	240 V
Main Output Voltage	230 V
Rated Power In W	1400 W
Rated Power In Va	2000 VA
Product Or Component Type	Uninterruptible power supply (UPS)
Input Connection Type	IEC 60320 C14
Output Connection Type	6 universal receptacle
Number Of Cables	1
Battery Type	Lead-acid battery
Provided Equipment	Documentation CD
	User manual
	USB cable

### **Batteries & Runtime**

Run Time	View Runtime Graph ☐
Efficiency	View Efficiency Graph ☐
Number Of Battery Filled Slots	0
Number Of Battery Free Slots	0
Battery Recharge Time	4 h
Battery Voltage	48 V
Battery Charger Power	75 W rated
Battery Life	35 year(s)
Replacement Battery	APCRBCV208 ☐
Extended Runtime	0

#### **General**

Number Of Power Module Free Slots	0
Number Of Power Module Filled Slots	0

Redundant	No
Ups Size	WS

# **Physical**

Colour	Black	
Height	24 cm	
Width	18 cm	
Depth	45.5 cm	
Net Weight	23.5 kg	
Mounting Preference	No preference	
Mounting Mode	Not rack-mountable	
Two Post Mountable	0	
Usb Compatible	No	

## Input

Network Frequency	4565 Hz +/- 1 Hz auto-sensing
Input Voltage Limits	165295 V

## Output

Maximum Configurable Power In W	1400 W
Output Frequency	50/60 Hz +/- 1 Hz unsynchronised
Crest Factor	3:1
Ups Type	Line interactive
Wave Type	Sine wave
Graph Display	1
Maximum Configurable Power In Va	2000 VA
Transfer Time	2-6 ms typical : 12 ms maximum

## Conformance

Product Certifications	CE
	TISI

### **Environmental**

Ambient Air Temperature For Operation	040 °C
Relative Humidity	095 % non-condensing
Operating Altitude	03000 m
Ambient Air Temperature For Storage	-1040 °C
Storage Relative Humidity	095 % non-condensing
Storage Altitude	015000 m
Acoustic Level	45 dBA
Ip Degree Of Protection	IP20

## **Communications & Management**

Alarm

Alarm when on battery : distinctive low battery alarm : overload continuous tone

### **Surge Protection and Filtering**

Surge Energy Rate

125 J

### **Packing Units**

Unit Type Of Package 1	PCE
	T OL
Number Of Units In Package 1	1
Package 1 Height	41.05 cm
Package 1 Width	32.6 cm
Package 1 Length	60.1 cm
Package 1 Weight	26.9 kg

### **Contractual warranty**

Warranty

2 years repair or replace



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

Learn more about Green Premium >





Transparency RoHS/REACh

### Well-being performance

Mercury Free

Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information