

Product datasheet

Specifications

APC Replacement Battery Cartridge #164 with 2 Year Warranty



APCRBC164

Overview

Lead time Usually in Stock

Main

Main Input Voltage 12 V DC
Product or component type Replacement battery cartridge
Battery type Lead-acid battery
Provided equipment Installation guide

Physical

Colour Black
Height 10.5 cm
Width 15.1 cm
Depth 6.5 cm
Net weight 3 kg
Mounting mode Not rack-mountable

Output

Battery capacity 9.4 Ah

Environmental

Ambient air temperature for operation 0...45 °C
Operating altitude 0...10000 ft
Relative humidity 0...95 % non-condensing
Ambient air temperature for storage -15...45 °C
Storage altitude 0.00...15240.00 m
Storage Relative Humidity 0...95 % non-condensing

Batteries & Runtime

Number of battery free slots 0

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number of battery filled slots	0
Battery voltage	12 V
Number of battery replacement quantity	1
Replacement battery	

Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	8.9 cm
Package 1 Width	21.3 cm
Package 1 Length	17.5 cm
Package 1 Weight	3.5 kg
Number of Units in Package 3	240
SCC14	10731304346866

Offer Sustainability

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
-------------------	--

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Recommended replacement(s)