

# Product datasheet

Specifications



## Rack ATS, 208V, 20A, C20 in, (8) C13 (1) C19 out



AP4434

⚠ To be discontinued on: 30 December 2022

⚠ To be discontinued

### Overview

Lead time Usually in Stock

### Main

Main Input Voltage	208 V
Main Output Voltage	208 V
Input Connection Type	IEC 60320 C20
Number of rack unit	1U
Provided equipment	Mounting hardware Rack mounting brackets Serial configuration cable

### Physical

Colour	Black
Height	4.4 cm
Width	43.2 cm
Depth	23.6 cm
Net weight	3.74 kg
Mounting location	Front Rear
Mounting preference	No preference
Mounting mode	Rack-mounted

### Input

Network frequency	50/60 Hz
Max line current	20 A
Input current limits	20 A
Load capacity	3300 VA

### Output

Max current draw	20 A
Number of power socket outlets	8 IEC 60320 C13

Protection type	Without circuit breaker
-----------------	-------------------------

## Conformance

Product certifications	cUL listed CE UL listed
Standards	EN 55022 class A FCC part 15 class A

## Environmental

Ambient air temperature for operation	-5...45 °C
Relative humidity	5...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-25...65 °C
Storage Relative Humidity	5...95 %
Storage altitude	0.00...15240.00 m

## Packing Units

Package 1 Weight	5.51 kg
Package 1 Height	11.4 cm
Package 1 width	60 cm
Package 1 Length	35.6 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Lead free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>
Take-back	Take-back program available

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------