Product datasheet

Specifications



Rack ATS, 120V, 30A, L5-30P in, (16) 5-20R out



AP4453

! Discontinued on: 9 Jun 2023



Overview

Lead Time Usually in Stock

Main

Main Input Voltage	120 V
Main Output Voltage	120 V
Input Connection Type	NEMA L5-30P
Number Of Rack Unit	2U
Cable Length	2.44 m
Number Of Cables	2
Provided Equipment	Mounting hardware Rack mounting brackets Serial configuration cable

Physical

Colour	Black
Height	8.8 cm
Width	43.2 cm
Depth	23.6 cm
Net Weight	6.33 kg
Mounting Location	Front Rear
Mounting Preference	No preference
Mounting Mode	Rack-mounted

Input

Network Frequency	50/60 Hz
[In] Rated Current	24 A
Max Line Current	30 A
Input Current Limits	30 A
Load Capacity	2880 VA

Output

Max Current Draw 30 A

Number Of Power Socket Outlets	16 NEMA 5-20R
Protection Type	Circuit breaker

Conformance

Standards	EN 55022 class A
	FCC part 15 class A

Environmental

Ambient Air Temperature For Operation	-545 °C
Relative Humidity	595 %
Operating Altitude	010000 ft
Ambient Air Temperature For Storage	-2565 °C
Storage Relative Humidity	595 %
Storage Altitude	0.0015240.00 m

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	21 cm
Package 1 Width	35.6 cm
Package 1 Length	58.4 cm
Package 1 Weight	8.82 kg

Contractual warranty

Warranty 2 years repair or replace



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Learn more about Green Premium >







Take-back Transparency RoHS/REACh

Resource performance



Take-Back Program Available

Well-being performance



Lead Free



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information