

# Product datasheet

Specifications



## APC 17" Rack LCD Console - Russian

AP5717R

### Overview

Lead time Usually in Stock

### Main

Main Input Voltage 100 V  
240 V

Number of rack unit 1U

Provided equipment C13-C14 power cord  
Documentation CD  
Firmware upgrade cable  
Installation guide  
NEMA 5-15 power cord  
PS2 KVM cable  
Rack mounting hardware  
Single user rack mount kit  
USB cable  
USB KVM cable

### Physical

Colour Black

Height 4.4 cm

Width 48.2 cm

Depth 61.4 cm

Net weight 15.9 kg

Mounting location Front  
Rear

Mounting preference No preference

Mounting mode Rack-mounted

Maximum mounting depth 104.98 cm

Minimum mounting depth 68 cm

### Input

Network frequency 50/60 Hz

### Conformance

Product certifications C-Tick  
GOST  
Industry Canada  
NOM  
UL listed

<b>Standards</b>	EN 55022 class A EN 55024 EN 60950 FCC part 15 class A IEC 60950
------------------	--

## Environmental

<b>Ambient air temperature for operation</b>	0...40 °C
--	-----------

## Supported Hardware

<b>Display colour</b>	16 colours
<b>Display size</b>	17 inch
<b>Trackball type</b>	PS/2 touchpad USB mouse
<b>Display type</b>	LCD display
<b>Display power consumption</b>	19 W
<b>Pixel size</b>	0.26

## Packing Units

<b>Package 1 Weight</b>	19.46 kg
<b>Package 1 Height</b>	15.2 cm
<b>Package 1 width</b>	67.3 cm
<b>Package 1 Length</b>	82.6 cm

## Offer Sustainability

<b>Sustainable offer status</b>	Green Premium product
<b>REACH Regulation</b>	<a href="#">REACH Declaration</a>
<b>REACH free of SVHC</b>	Yes
<b>EU RoHS Directive</b>	Compliant <a href="#">EU RoHS Declaration</a>
<b>Lead free</b>	Yes
<b>Take-back</b>	Take-back program available

## Contractual warranty

<b>Warranty</b>	2 years repair or replace
-----------------	---------------------------